

ADAPTIVE GRIPPERS







2F- 140



Machine Tending



Assembly



Pick & Place











- Plug + Play kits for Universal Robots
 - Wide range of applications
 - Easy to customize
- Fast installation
- Easy & powerful user interface
- Adjustable stroke, speed & force
- Robust, factory-proven hardware
 - High pinch force & payload
 - Built-in part validation

START PRODUCTION FASTER



TAKE FULL CONTROL

ADJUST THE GRIPPER'S POSITION, SPEED, AND **FORCE FOR A PERFECT GRASP**

DETECT IF A PART IS PICKED AND VALIDATE ITS DIMENSION

USE ANY ADAPTIVE GRIPPER WITH THE SAME EASY-TO-USE INTERFACE



PLUG + PLAY KITS FOR UR

INSTALL HARDWARE EASILY, PROGRAM SOFTWARE QUICKLY - AND GET YOUR ROBOT TO WORK SOONER

SPECIFICATIONS	2F-85	2F-140
Stroke (adjustable)	85 mm	140 mm
Grip force (adjustable)	20 to 235 N	10 to 125 N
Form-fit grip payload	5 kg	2.5 kg
Friction grip payload	5 kg	2.5 kg
Gripper mass	0.9 kg	1 kg
Position resolution (fingertip)	0.4 mm	0.6 mm
Closing speed (adjustable)	20 to 150 mm/s	30 to 250 mm/s
Communication protocol	Modbus RTU (RS-485)	
Ingress protection (IP) rating	IP40	IP40
* All specifications provided for reference only. See user manual at support.robotiq.com for official specifications.		

WHAT'S NEXT?

Get access to the Adaptive Grippers specifications at

support.robotiq.com

Chat with the Robotiq sales team: iss@robotiq.com 1-888-ROBOTIQ

Place your contact information here







Updated May 2020 robotiq.com